

[See all 10 Products in Family](#)

**TECHSPEC® 10mm Diameter 45° Rod Mirror Aluminum Coated**



45° Rod Mirrors

Stock #45-944 **20+ In Stock**

1 MRP ₹15,941

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹15,941 each
Qty 6-25	₹14,326 each
Qty 26-49	₹12,712 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Rod Lens **Type:**

Coating on Elliptical Surface **Note:**

**Physical & Mechanical Properties**

Diameter (mm):

10.00 +0.00/-0.05

15.00

Length (mm):

Bevel:

Protective as needed

Length Tolerance (mm):

±0.1

## Optical Properties

Coating:

Protected Aluminum (400-700nm)

Substrate:

N-BK7

Surface Quality:

40-20

Angle Tolerance (arcmin):

±10

Coating Specification:

$R_{avg} > 85\%$  @ 400 - 700nm

Ray Deviation (°):

90

Wavelength Range (nm):

400 - 700

Coating Type:

Metal

Damage Threshold, By Design:

0.3 J/cm<sup>2</sup> @ 532nm & 1064nm, 10ns

## Regulatory Compliance

RoHS 2015:

Compliant

Reach 219:

Compliant

Certificate of Conformance:

[View](#)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Protected Aluminum Coating
- Reflect Light at 90°

TECHSPEC® 45° Rod Mirrors are designed for use in a variety of laser and imaging systems. The mirrors can be used to redirect laser light at 90°. Their small diameters make them ideal for use in fiberscope/borescope applications where size is critical. TECHSPEC 45° Rod Mirrors feature polished elliptical surfaces and ground circumferences and bases. These components are available in a range of micro sizes for integration into a host of OEM applications.

## Technical Information

