


[See all 4 Products in Family](#)

10mm Dia. x 25mm FL, Grade 1, Achromatic Lens



Stock #06-386 CLEARANCE **20+ In Stock**

₹1,736

ADD TO CART

Volume Pricing	
Qty 1+	₹1,736 each
Need More?	Request Quote

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

10.00 **Diameter (mm):**

Protective as needed **Bevel:**

Optical Properties

Effective Focal Length EFL (mm):

25.00

2.5

f#:

0.2

Numerical Aperture NA:

Anti-Reflection Coating

Coating:

Material Properties

Grade 1

Grade:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Japan

Country of Origin:

Edmund Optics India Private Limited

Imported By:

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Achromatic doublet lenses consist of two optical components cemented together to form an achromatic doublet which is optimized to correct for on-axis spherical and chromatic aberrations. Achromatic doublet lenses are far superior to simple lenses for multi-color ("white light") imaging. The two elements composing an achromatic doublet lens (literally, "a lens with no color") are paired together for their ability to correct the color separation inherent in glass.

1 - 24.9mm Experimental Quality Achromatic Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

