

TECHSPEC[®] 1.0mm Diameter, N-BK7 Half-Ball Lens



TECHSPEC[®] N-BK7 Half-Ball Lenses

Stock **#49-568** 20+ In Stock

-

1

+

₹3,854

ADD TO CART

Volume Pricing	
Qty 1-10	₹3,854 each
Qty 11-49	₹3,464 each
Need More?	Request Quote

Product Downloads

General

Type:

Half-Ball Lens

Physical & Mechanical Properties

Diameter (mm):

1.00

Center Thickness Tolerance (mm):

±0.05

Radius R (mm):

0.50	
	Radius Tolerance (μm):
+0.0/-1.5	
	Thickness (mm):
0.50	
	Diameter Tolerance (μm):
±2.5	

Optical Properties

N-BK7	Substrate: 
Uncoated	Coating:
	Wavelength Range (nm):
350 - 2200	

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
Switzerland	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Fiber Coupling Half-Spheres
- Collimating Lenses

TECHSPEC® N-BK7 Half-Ball Lenses are ideal for applications such as fiber communication, endoscopy, microscopy, optical pick-up devices, and laser measurement systems. Half-ball (hemispherical) lenses can be interchanged with full ball lenses if the physical constraints of an application require a more compact design. These collimating lenses are uncoated, with a wavelength range of 350-2200nm. TECHSPEC® N-BK7 Half-Ball Lenses are offered in diameters ranging from 0.50 to 10.00mm.

Technical Information

