

[See all 69 Products in Family](#)

TECHSPEC[®] 10mm Diameter x 1.75mm Thickness, MgF₂ Coated, BOROFLOAT[®] Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock **#83-370** **20+ In Stock**

-

1

+

₹2,109

ADD TO CART

Volume Pricing	
Qty 1-5	₹2,109 each
Qty 6-25	₹1,705 each
Qty 26-99	₹1,540 each
Need More?	Request Quote

Product Downloads

General

Type:

Protective Window

Physical & Mechanical Properties

Clear Aperture CA (mm):

9.00

Diameter (mm):

10.00 ±0.5	
1.75 ±0.2	Thickness (mm):
Protective as needed	Bevel:
≥90	Clear Aperture (%):
Ground	Edges:
0.20	Poisson's Ratio:
64	Young's Modulus (GPa):
480.00	Knoop Hardness (kg/mm²):

Optical Properties

MgF ₂ (400-700nm)	Coating:
BOROFLOAT®	Substrate: ☐
1.472	Index of Refraction (n _d):
80-50	Surface Quality:
≥95	Transmission (%):
65.41	Abbe Number (v _d):
R _{abs} ≤2.5% @ 550nm	Coating Specification:
400 - 700	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):

Material Properties

2.23	Density (g/cm³):
525	Transformation Temperature (°C):
3.25 (+20 to +300°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Environmental & Durability Factors

1 hour @ 500; >100 hours @ 450	Operating Temperature (°C):
Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term, >100 hrs: 80K	Resistance to Temperature Difference (K):
Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 - 15mm Thick: 150K	Thermal Shock (K):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details


- Low Coefficient of Thermal Expansion
- Visible to Near Infrared Transmission
- High Resistance to Thermal Shock

TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C). TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness — typically 4 - 6λ per inch.

BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



Coating Curves

Quote Your Size

Compatible Mounts