

[See all 5 Products in Family](#)

## 10mm FL, 632nm, Visible Metalens Plate



Stock #86-931 **NEW** 3 In Stock

- 1 + MRP ₹75,668

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹75,668 each
Qty 10+	₹68,101 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Note:**  
Black absorptive aperture applied to metasurface

### Physical & Mechanical Properties

**Dimensional Tolerance (mm):**  
+/-0.2

**Thickness (mm):**  
0.70 ±0.07

**Outer Dimensions (mm):**

20.0 x 20.0

Inner Diameter (mm):

4

## Optical Properties

Effective Focal Length EFL (mm):

10.00 ±2%

Substrate:

Eagle XG

Numerical Aperture NA:

0.20

Coating:

Broadband 420-670nm AR Coating, backside  
Protective Overcoat, frontside

Coating Specification:

Broadband 420-670nm AR-Coating (Back surface only)

$R_{\text{abs}} \leq 1\%$  from 420-670nm

$R_{\text{avg}} \leq 0.4\%$  from 420-670nm

Design Wavelength DWL (nm):

632

Index of Refraction ( $n_d$ ):

1.5198 (435.8 nm), 1.5078 (643.8 nm)

Transmission (%):

76

## Material Properties

Thermal Expansion:

$31.7 \times 10^{-7} \text{ }^\circ\text{C}^{-1}$  (0-300°C)

## Environmental & Durability Factors

Environmental Durability:

$\geq 200\text{C}$ , 1000hrs

## Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Flat, Space Saving Alternative to Traditional Lenses
- Nanostructure Design Enables Efficient Manipulation of Light
- Compact 0.7mm Thickness for Easy Integration into a Variety of Applications

Visible Metalens Plates are designed with an innovative nanostructure design to manipulate and focus light, offering a highly compact and high-performance alternative to traditional curved lenses. Featuring ultra-thin Eagle XG substrates, these lens plates are available for 532nm and 632nm design wavelengths in a range of focal lengths. These metalenses are available in a single lens construction, where an individual metalens is centered on the plate and surrounded by an absorptive aperture to reduce stray light, or an array construction, where one of each of the four smaller Metalenses are arranged on a single plate for versatility. Visible Metalens Plates are ideal for low SWaP, LIDAR, imaging, and beam shaping applications.

**Note:** The Metalens surface is very delicate, and contact should be avoided during cleaning and handling. Visible Metalens Plates should be cleaned only using compressed air.