

TECHSPEC® 10mm Dia. x 40mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#63-721** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹6,743.00**

ADD TO CART

Qty 1-5
₹6,743.00
Qty 6+
₹5,394.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.025

Effective Focal Length EFL (mm):
40.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 37.79
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 9.00
Centering (arcmin): <1
Center Thickness CT (mm): 4.50 ±0.10
Center Thickness CT 1 (mm): 3.00 ±0.05
Center Thickness CT 2 (mm): 1.50 ±0.05
Radius R₁ (mm): 23.66
Radius R₂ (mm): -18.11
Radius R₃ (mm): -55.78
Edge Thickness ET (mm): 3.74
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 4.00
Numerical Aperture NA: 0.13
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View