

TECHSPEC[®] 10mm Dia x 8mm FL, NIR I Coated, Molded Aspheric Condenser Lens



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#15-728**

10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹4,611.00

ADD TO CART

Qty 1-10
₹4,611.00
Qty 11+
₹4,089.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.2

Effective Focal Length EFL (mm):
8.00 @ 587.6nm

Numerical Aperture NA:
0.625

Back Focal Length BFL (mm): 3.2
Substrate: ☐ Liba2000+
Focal Length Tolerance (%): ±5
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2
Clear Aperture CA (mm): 8.78
Edge Thickness ET (mm): 3.22
Center Thickness CT (mm): 6.79 ±0.30
f#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 10.00
Radius R₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant