

[See all 13 Products in Family](#)

10mm x 10mm XP-NIR Commercial Grade NIR Polarizing Film



Stock **#73-351** **20+ In Stock**

MRP ₹2,572

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹2,572 each
Qty 10+	₹2,058 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Note:
 Delivered with protective film on both sides
 Polarization axis indicated by notch cut into edge
 (circular parts) or stripe on protective film
 Pressure Sensitive Adhesive (PSA) on one side

Physical & Mechanical Properties

Length (mm):

10.00	Dimensions (mm):
10 x 10 +0/-0.3	
0.21 +/- 0.025	Thickness (mm):
Polarizing Film	Construction:
10.00	Width (mm):

Optical Properties

Uncoated	Coating:
>160:1 from 800-1000nm (Average, Typical)	Extinction Ratio:
XP-NIR Polarizing Film	Substrate: □
800 - 1000	Wavelength Range (nm):
>99.0 @ 860nm	Polarization Efficiency (%):
35 +/- 3.0 @ 860nm	Transmission, Single (%):

Environmental & Durability Factors

105C x 500h (dry) Change in single transmittance @ 870nm <+/-5% 60C x 1000h (90% humidity) Change in single transmittance @ 870nm <+/-5% from initial value, change in polarization efficiency @ 870nm <-3% from initial value	Heat Resistance (°C x Hours):
-40C x 1000h Change in single transmittance @ 870nm <+/-5% from initial value Change in polarization efficiency @ 870nm <-3% from initial value	Cold Resistance (°C x Hours):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Optimized Performance Between 800-1000nm
- Ideal for Sensing and Inspection Applications
- Available in Sizes up to 600 x 900mm
- [Near-Infrared \(NIR\) Linear Polarizing Film](#) and [High Contrast Near-Infrared \(NIR\) Polarizing Film](#) also Available for Broadband IR Applications

Commercial Grade NIR Polarizing Film (XP-NIR) offers a cost-effective solution for polarization applications in the 800-1000nm range. This film offers contrast ratios of >160:1 (Average) and >99% polarization efficiency in the specified range, and its high environmental resistance makes it a great choice for demanding environments. Commercial Grade NIR Polarizing Film (XP-NIR) is delivered with a pressure sensitive adhesive (PSA) on one side and is available in circular or rectangular sizes, with up to a 50mm diameter or a 600 x 900mm format. This film is ideal for commercial sensing, inspection, and LIDAR applications.

Note: Custom sizes available up to 1000mm

Technical Information

