

TECHSPEC® 10mm NIR I Coated, N-BK7 Right Angle Prism (Leg Coated)



Stock #84-522 **3 In Stock**

MRP ₹12,309

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹12,309 each
Qty 6-25	₹9,887 each
Qty 26-49	₹9,333 each
Need More?	Request Quote

Product Downloads

General

Right Angle Prism **Type:**
Coating on Entrance/Exit Faces **Note:**

Physical & Mechanical Properties

Dimensional Tolerance (mm):
+0.00/-0.10

Protective as needed	Bevel:
90	Clear Aperture (%):
14.10	Length of Hypotenuse (mm):
10.00	Length of Legs (mm):
Optical Properties	
±15	Angle Tolerance (arcsec):
NIR I (600-1050nm)	Coating:
N-BK7	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
Left-Handed	Image Orientation:
Entrance/Exit Faces: $R_{avg} \leq 0.5\%$ @ 600 - 1050nm	Coating Specification:
90	Ray Deviation (°):
600 - 1050	Wavelength Range (nm):
Entrance/Exit Faces: 7 J/cm^2 @ 1064nm, 10ns	Damage Threshold, By Design: <input type="checkbox"/>
1.25	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Singapore	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Ideal for Low Power Laser Sources
- Multiple BBAR Coatings Available
- Ray Deviation of 90°

TECHSPEC® Broadband Anti-Reflection (BBAR) Coated N-BK7 Right Angle Prisms (Leg Coated) are ideal for a range of low power laser line applications. These prisms feature tight angle tolerances and a precision N-BK7 substrate. The BBAR coating improves transmission efficiency when compared to uncoated right angle prisms. TECHSPEC® Broadband Anti-Reflection (BBAR) Coated N-BK7 Right Angle Prisms (Leg Coated) have their BBAR coating on entrance and exit faces. The prisms are available in lengths from 5 to 50mm.

Right angle prisms are generally used to bend image paths or redirect light at 90°. This produces a left-handed image and depending on the orientation of the prism, the image may be inverted or reverted. Right angle prisms can also be used in combination for image/beam displacement.

Technical Information



Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram