

[See all 15 Products in Family](#)

Richardson Gratings™ 1200 Grooves, 25 x 25mm, 400-1200nm, Plane Holographic Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Reflective Holographic Diffraction Gratings



Stock #15-746 **11 In Stock**

MRP ₹18,160

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹18,160 each
Qty 10-24	₹16,344 each
Need More?	Request Quote

Product Downloads

General

Reflective Diffraction Grating

Type:

220H

Master Reference:

Physical & Mechanical Properties

25.0 x 25.0 ±0.1 **Dimensions (mm):**

>90 **Clear Aperture (%):**

Holographic Grating **Construction:**

25.00 **Length (mm):**

6.00 ±0.5 **Thickness (mm):**

25.00 **Width (mm):**

±1 **Centering of Ruled Area on Substrate (mm):**

±0.15 **Alignment of Grooves to Edge (°):**

<0.05 **Groove Spacing Tolerance (%):**

Optical Properties

1200 **Groove Density (grooves/mm):**

400 - 1200 **Wavelength Range (nm):**

700 **Blaze Wavelength (nm):**

Aluminium **Coating:**

Float Glass **Substrate:**

λ/4 **Reflected Wavefront, RMS:**

S, P and Average **Polarization:**

1 **Spectral Order (m):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Diffraction Efficiency
- Reduced Stray Light and More Accurate Periodicity than Ruled Gratings
- Wavelength Options from UV to NIR Regions Available
- Custom Sizes Available

Richardson Gratings™ High Precision Reflective Holographic Diffraction Gratings display reduced light scattering compared with ruled gratings, making them ideal for stray light sensitive applications such as Raman spectroscopy. The gratings are recorded in a photoresist by exposure to an intense laser interference pattern and then chemically developed to reveal a fringe pattern with a sinusoidal cross section. Gratings for use from the UV to NIR spectral regions are available.

Note: The surface of these gratings is very sensitive and should never be touched when handling the optic. If cleaning is required to remove dust particles, non-contact cleaning using clean compressed air is recommended.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools