

TECHSPEC[®] 1:1 with 50mm and 50mm EFL Achromats, 30mm Achromatic Pair



TECHSPEC Mounted Achromatic Lens Pairs

Stock **#46-011** [CONTACT US](#)

-

1

+

₹18,373

ADD TO CART

Volume Pricing	
Qty 1-5	₹18,373 each
Qty 6-25	₹14,714 each
Qty 26-49	₹14,247 each
Need More?	Request Quote

Product Downloads

General

Relay Lens

Type:

Physical & Mechanical Properties

22.0

Clear Aperture CA (mm):

3.70

Center Air Spacing (mm):

30 +0.0/-0.10	Housing Diameter (mm):
34 ±0.2	Housing Length (mm):
8	Lens Edge Spacing at Mount (mm):
39.68	Image Distance (mm):

Achromat Pair in Anodized Aluminum Housing	Construction:
--	---------------

Optical Properties

N-BAF10 / N-SF10 / N-BAF10 / N-SF10	Substrate: □
40-20	Surface Quality:
f/2.26	Working f#:
MgF ₂ (400-700nm)	Coating:
R _{avg} ≤1.75% @ 400 - 700nm	Coating Specification:
50.00	Effective Focal Length EFL A (mm):
50.00	Effective Focal Length EFL B (mm):
1:1	Magnification:
39.68	Object Distance (mm):
400 - 700	Wavelength Range (nm):

Regulatory Compliance


Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- 15mm and 30mm Diameter Options
- AR Coated Lenses
- Mounted Achromatic Pairs Kits Available

TECHSPEC® Mounted Achromatic Lens Pairs combine popular TECHSPEC® Achromats into common configurations used for relay and projection applications. Packaged in slim-line aluminum housing, each pair is ready for integration into a host of OEM applications, eliminating the need to handle loose optics. 15.0mm pairs can be coupled into C-mount components using [Helicoid Barrel Accessory](#). TECHSPEC Mounted Achromatic Lens Pairs have also been oriented for optimum system performance. All lenses, 15.0mm and 30.0mm, are AR coated. Lower f# pairs may not be ideal for imaging applications depending on the performance requirements. Cylinder lenses can be incorporated into empty barrels in order to generate lines or sheets of light.

Technical Information



Coating Curves

