

[See all 37 Products in Family](#)

Richardson Gratings™ 1200 Grooves, 25 x 25mm, 750nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock #37-137 **15 In Stock**

1 MRP ₹19,674

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹19,674 each
Qty 10-24	₹17,706 each
Need More?	Request Quote

Product Downloads

General

Reflective Diffraction Grating **Type:**

2917 **Master Reference:**

Physical & Mechanical Properties

25.0 x 25.0 ±0.1	Dimensions (mm):
>90	Clear Aperture (%):
Ruled Grating	Construction:
25.00	Length (mm):
6.00 ±0.5	Thickness (mm):
25.00	Width (mm):
±1	Centering of Ruled Area on Substrate (mm):
±0.15	Alignment of Grooves to Edge (°):
<0.05	Groove Spacing Tolerance (%):

Optical Properties

1200	Groove Density (grooves/mm):
450 - 1500	Wavelength Range (nm):
750 ±25	Blaze Wavelength (nm):
26.7	Blaze Angle (°):
91	Peak Efficiency, Typical (%):
Aluminium	Coating:
Float Glass	Substrate: <input type="checkbox"/>
λ/4	Reflected Wavefront, RMS:
S and P	Polarization:
1	Spectral Order (m):

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Excellent Efficiency at Blaze Wavelength and Blaze Angle
- Superior Dimensional Tolerances
- Ideally Suited for Spectroscopic Applications
- Custom Sizes Available

Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings are designed for consistent, predictable performance. The gratings are manufactured from highly accurate masters to provide a high level of repeatability to simplify OEM system designs by reducing the need for tedious alignment adjustments. With λ/4 reflected wavefronts and up to 90% diffraction efficiency, these gratings are specified to meet the needs of the most demanding applications such as high-resolution spectroscopy. Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings feature bare aluminum coatings, allowing for options that range from 250 to 10,000nm with excellent peak efficiencies. Custom sizes available on request.


Note: The surface of these gratings is very sensitive and should never be touched when handling the optic. If cleaning is required to remove dust particles, non-contact cleaning using clean compressed air is recommended.

Technical Information


Typical Efficiency Curves for High Precision Reflection Gratings
Optimized (Blaze) Wavelengths from 1200 - 1850nm



Typical Efficiency Curves for High Precision Reflection Gratings
Optimized (Blaze) Wavelengths from 750 - 900nm



Typical Efficiency Curves for High Precision Reflection Gratings
Optimized (Blaze) Wavelengths from 300 - 400nm



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools