

1.1mW 635nm 30°, VLM™2 Laser Line Focusable



Stock #52-896 **3 In Stock**

- 1 + MRP ₹31,435

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹31,435 each
Need More?	Request Quote

Product Downloads



General

Diode	Type of Laser:
IIIa	Laser Class - CDRH:

Physical & Mechanical Properties

28.00	Weight (g):
0.58	Diameter (inches):

1.82 Length (inches):

Optical Properties

635.00 Wavelength (nm):

1.00 Beam Width (mm):

Red Color:

30.00 Fan Angle (°):

Face of module to past collimation Focus Range (mm):

Electrical

50/70 (Typical/Maximum) Operating Current (mA):

1.1 Output Power (mW):

±4 Output Power Tolerance (%):

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately.
USA: [#59-099](#)
Europe: [#35-201](#)
Japan: [#59-099](#)
Korea: [#33-771](#)
China: [#59-099](#)

5-10 DC Output Voltage (V):

Free Space Output Type:

Environmental & Durability Factors

-10 to +40 Operating Temperature (°C):

Regulatory Compliance

[Exempt](#) RoHS 2015:

[Contains SVHC\(s\)](#) Reach 224:

[View](#) Certificate of Conformance:

Thailand Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Bright 635nm Beam, 1.1mW and 1.4mW Models
- Non-Rotating Optics
- Non-Intrusive Built-in Focusing Mechanism
- Recommended Power Supply: [#59-099](#)

By combining the robust package of our popular [Visible Laser Modules \(VLM™\)](#) with the convenience of focusing, the VLM™ 2 Focusable Laser Modules offer a dramatic increase in line definition at variable working distances. These focusing laser modules are ideal for machine vision, medical diagnostics and manufacturing applications. All have a locking knurled outer ring to keep the beam at desired focus. Additional features include: green on/off LED, 24" leads, fully shielded drive circuitry and reverse polarity protection. ESD Class 2 protection to ML-STD-1686C and CDRH certified. [Power Supply](#), required for operation, sold separately.

Technical Information

