

TECHSPEC[®] 12.7mm Dia. 266nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC[®] Nd:YAG Laser Line Mirrors

Stock #38-833 10 TO 12 DAYS

-

1

+

₹12,528.00

ADD TO CART

Qty 1-5
₹12,528.00
Qty 6+
₹11,049.00
Volume Pricing
Request Quote

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):

90
Back Surface: Commercial Polish
Reflection at DWL (%): 99.8
Coating Specification: R _{abs} >99.8% @ 266nm
Wavelength Range (nm): 263 - 268
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (266nm)
Design Wavelength DWL (nm): 266
Diameter (mm): 12.70 +0.00/-0.10
Thickness (mm): 6.35 ±0.2
Angle of Incidence (°): 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 2 J/cm ² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View