

# Richardson Gratings™ 1200 Grooves, 12.7 x 12.7mm, 400-1200nm, Plane Holographic Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Reflective Holographic Diffraction Gratings



Stock **#15-745** 10 TO 12 DAYS

- 1 + **₹11,745.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1+                        |
| ₹11,745.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Groove Density (grooves/mm):  
1200

Wavelength Range (nm):  
400 - 1200

|                                                           |
|-----------------------------------------------------------|
| <b>Blaze Wavelength (nm):</b><br>700                      |
| <b>Dimensions (mm):</b><br>12.7 x 12.7 ±0.1               |
| <b>Clear Aperture (%):</b><br>>90                         |
| <b>Coating:</b><br>Aluminium                              |
| <b>Construction:</b><br>Holographic Grating               |
| <b>Length (mm):</b><br>12.70                              |
| <b>Substrate:</b> <input type="checkbox"/><br>Float Glass |
| <b>Thickness (mm):</b><br>6.00 ±0.5                       |
| <b>Type:</b><br>Reflective Diffraction Grating            |
| <b>Width (mm):</b><br>12.70                               |
| <b>Reflected Wavefront, RMS:</b><br>λ/4                   |
| <b>Centering of Ruled Area on Substrate (mm):</b><br>±1   |
| <b>Alignment of Grooves to Edge (°):</b><br>±0.15         |
| <b>Groove Spacing Tolerance (%):</b><br><0.05             |
| <b>Polarization:</b><br>S, P and Average                  |
| <b>Master Reference:</b><br>220H                          |
| <b>Spectral Order (m):</b><br>1                           |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br>Compliant                                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |