

TECHSPEC[®] 1200nm, 25mm Diameter, Low GDD Dichroic Shortpass Ultrafast Filter



TECHSPEC[®] Low GDD Dichroic Shortpass Ultrafast Filters

Stock #14-035 10 TO 12 DAYS

-

1

+

₹16,008.00

ADD TO CART

Qty 1-5
₹16,008.00
Qty 6+
₹12,789.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):
45

Cut-Off Wavelength (nm):
1,200.00

Substrate: Fused Silica (Coming 7980)
Coating: Hard Coated
P-Polarization Transmission (%) : >80
Reflection (%) : >97 Average Polarization
Reflection Wavelength (nm) : 1260 - 1560
S-Polarization Transmission (%) : >80
Surface Quality : 60-40
Thickness (mm) : 1.05 ±0.1
Transmission (%) : >85 Average Polarization
Transmission Wavelength (nm) : 624 - 1152
Type : Dichroic Filter
Dimensional Tolerance (mm) : +0.0/-0.2
Transmitted Wavefront, RMS : λ/4
Slope Factor (%) : 3.00
Cut-Off Tolerance (%) : ±2
S-Polarization Reflection (%) : >95
P-Polarization Reflection (%) : >95
Coating Specification : Surface 1: Hard Dielectric Sputtered Surface 2: MgF ₂
Wavelength Range (nm) : 624 - 1560
GDD Specification (Transmission) : 0 ±100fs ² @ 840 - 1152nm 0 ±500fs ² @ 624 - 1152nm

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant