See all 102 Products in Family

TECHSPEC® 12.0mm Diameter x 24.0mm FL, 1064nm V-Coat, PCX Lens

633nm Laser Line Coated Plano-Convex (PCX) Lenses

Stock **#65-540** **4 In Stock**

Other Coating Options

- 1 + **MRP** ₹5,348

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	**₹5,348** each
Qty 10-25	**₹4,818** each
Qty 26-49	**₹4,263** each
Need More?	Request Quote

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):
12.00 +0.0/-0.025

Centering (arcmin):
<1

Center Thickness CT (mm):
2.80 ±0.05

Edge Thickness ET (mm):
1.25

Clear Aperture CA (mm):
11

Bevel:
Protective as needed

Optical Properties

Effective Focal Length EFL (mm):
24.00 @ 587.6nm

Back Focal Length BFL (mm):
22.15

Coating:
Laser V-Coat (1064nm)

Coating Specification:
R_{abs} <0.25% @ 1064nm

Substrate:
N-BK7

Surface Quality:
40-20

Power (P-V) @ 632.8nm:
1.5λ

Irregularity (P-V) @ 632.8nm:
λ/4

Focal Length Tolerance (%):
±1

Radius R_1 (mm):
12.42

f/#:
2.00

Numerical Aperture NA:
0.25

Design Wavelength DWL (nm):
1064

Damage Threshold, By Design:
5 J/cm^2 @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 235:
Compliant

Country of Origin:
Japan

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our custom manufacturing capabilities or submit an inquiry here.

Product Details

- <0.25% Reflection at 1064nm for Fiber and Nd:YAG Applications

- BBAR Coating Options Also Available: **uncoated**, **MgF_2**, **VIS 0°**, **VIS-NIR**, **NIR I**, **NIR II**
- **405nm**, **532nm**, **633nm**, **785nm**, **980nm**, 1064nm, and **1550nm** V-Coated Options Offered

TECHSPEC® 1064nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC ® 1064nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: **405nm**, **532nm**, **633nm**, **785nm**, **980nm**, and **1550nm**. Other coating options are available, including **uncoated**, **MgF2**, **VIS 0°**, **VIS-NIR**, **NIR I**, and **NIR II**.



Technical Information



Compatible Mounts

;