

[See all 2 Products in Family](#)

(12.5-75mm FL), 6X Manual Zoom Video Lens



#53-153

Stock #53-153 [CONTACT US](#)

- 1 + MRP ₹67,437

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹67,437 each
Need More?	Request Quote

Product Downloads

General

Macro Zoom Lens **Type:**

Physical & Mechanical Properties

114.50 **Length (mm):**

57.00 **Maximum Diameter (mm):**

475.00 **Weight (g):**

Optical Properties

Field of View @ Min Working Distance (mm):
495 - 86

Horizontal Field of View, 1/2" Sensor:
27.8° - 4.9°

Zoom Ratio:
6:1

Focal Length Range (mm):
12.5-75

Working Distance (mm):
1,000 - ∞

Aperture (f/#):
f/1.2 - f/16

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
2/3"

Threading & Mounting

Filter Thread:
M55.0 x 0.75

Mount:
C-Mount

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)

Country of Origin:
Japan

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Manual Zoom, Focus and Iris Control
- Features Locking Set Screws
- C-Mount

Manual Zoom Imaging Lenses provide manual adjustment of focal length (zoom), iris, and focus. Zoom lenses cover the focal length range of several fixed focal length lenses in one lens. Manual Zoom Imaging Lenses should be used when a variable angle field of view is required. Ideal applications include inspection, machine vision, and robotics.

Technical Information

