

TECHSPEC®

12.5" Diameter x 100" FL Protected Gold, Parabolic Mirror



Stock #32-277-566

10 TO 12 DAYS

-

1

+

₹297,105.00

ADD TO CART

Qty 1-2
₹297,105.00
Qty 3+
₹252,561.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate:

BOROLOAT®

SUPREMAX®

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 12.5 +0.06/-0
Diameter (mm): 317.50 +1.5/-0
Effective Focal Length EFL (inches): 100.0
Effective Focal Length EFL (mm): 2,540.00
Radius of Curvature (mm): 5,080.00
Aperture (f/#): f/8
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 286
Edge Thickness ET (inches): 2.13
Edge Thickness ET (mm): 54.10
Type: Parabolic Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant