

TECHSPEC® 12.5/12.7mm Optic Dia., Compact Kinematic Mount, 2-Screws



12.5/12.7mm Diameter Compact Kinematic Mount, 2-Screws, #34-720

Stock **#34-720** [CONTACT US](#)

- 1 + ₹8,482

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | ₹8,482 each |
| Qty 5-9 | ₹7,633 each |
| Qty 10+ | ₹7,046 each |
| Need More? | Request Quote |

Product Downloads

General

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Number of Adjustment Screws:
2

Plate Dimensions (mm):

Physical & Mechanical Properties

10.9 **Clear Aperture CA (mm):**

19.60 **Thickness (mm):**

No Z-Axis Translation **Travel (mm):**

Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings **Construction:**

±5 **Fine Tilt Angle (°):**

±5 **Fine Tip Angle (°):**

0.2 **Adjustment Screw Pitch (mm):**

1.9 **Min. Thickness of Compatible Optics (mm):**

15.0 **Centerline Height (mm):**

19.6 **Thickness of Front Plate to Back Plate (mm):**

1.3 **Pointing Stability (μrad):**

Threading & Mounting

12.5 - 12.7 **Size of Compatible Optics (mm):**

M4 x 0.7 **Compatible Post:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

China **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Product Details

- M3 x 0.2 Fine Adjustment Screw Threads
- <25mm Overall Profile
- Lockable for Improved Stability

Our TECHSPEC® Compact Kinematics are designed to retain the performance of a larger kinematic for integration into space sensitive applications. These kinematics feature completely resending adjustment screws for integration into OEM applications. TECHSPEC Compact Kinematic Mounts have two front plate models for utilization of set screw or adhesive optic securing. Stainless steel inserts are also used to ensure quality and stability. These kinematic mounts, in conjunction with our [TECHSPEC Laser Mirrors](#), are ideal for reliable integration into laser machining, cinema or life science applications.