

[See all 24 Products in Family](#)

TECHSPEC[®] 12.5mm 1064nm, Laser Line λ /20 High Tolerance Right Angle Mirror



Stock #37-661 3 In Stock

-

1

+

₹21,870

ADD TO CART

Volume Pricing	
Qty 1-5	₹21,870 each
Qty 6-25	₹17,460 each
Qty 26-49	₹16,470 each
Need More?	Request Quote

Product Downloads

General	
Right Angle Mirror	Type:
Physical & Mechanical Properties	
Protective as needed	Bevel:
90	Clear Aperture (%):

+0.00/-0.10	Dimensional Tolerance (mm):
17.70	Length of Hypotenuse (mm):
12.50	Length of Legs (mm):
Optical Properties	
Laser Mirror (1064nm)	Coating:
$\lambda/20$	Surface Flatness (P-V):
1064	Design Wavelength DWL (nm):
Fused Silica (Corning 7980)	Substrate: ☐
Coating Specification: R _{abs} >99.8% @ 1064nm @ 45° AOI R _{avg} >99.5% @ 1046 - 1074nm @ 45° AOI	
20-10	Surface Quality:
1MW/cm ² @ 1064nm	Damage Threshold, Reference: ☐
±1	Pyramid Tolerance (arcmin):
±15	Angle Tolerance (arcsec):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:
Singapore	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- >99.5% Reflectivity at the Design Wavelength
- ±15 Arcsecond Angular Tolerance
- High Thermal Stability Substrates

TECHSPEC® Laser Line $\lambda/20$ High Tolerance Right Angle Mirrors are designed at Nd:YAG wavelengths with durable, high reflectivity dielectric coatings. Right angle mirrors are easily mounted and integrated into systems that redirect light 90°. With ±15 arcsecond angular tolerance and ±1 arcminute pyramid tolerance, these laser line mirrors simplify alignment when mounting. TECHSPEC® Laser Line $\lambda/20$ High Tolerance Right Angle Mirrors feature laser induced damage threshold specifications making them ideal for demanding laser applications.

