

TECHSPEC® 12.5mm Dia, 0.50 Numerical Aperture VIS Coated, Aspheric Lens



Stock **#69-859** 10 TO 12 DAYS

[Other Coating Options](#)



1



₹18,705.00

ADD TO CART

Qty 1-5
₹18,705.00
Qty 6+
₹14,964.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Effective Focal Length EFL (mm):
12.50 @ 587.6nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 9.35
Substrate: L-BAL35
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (425-675nm)
Coating Specification: R _{avg} ≤1.5% @ 425 - 675nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 11.25
Edge Thickness ET (mm): 2.11
Center Thickness CT (mm): 5.00 ±0.1
f/#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 425 - 675
Conjugate Distance: Infinite
Power (diopters): 80.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant