

12.5 x 12.5mm 120 Grit Ground Glass Diffuser



Stock **#83-084** 20+ In Stock

-

1

+

₹1,357

ADD TO CART

Volume Pricing	
Qty 1-10	₹1,357 each
Qty 11+	₹1,155 each
Need More?	Request Quote

Product Downloads

General	
Ground Glass Diffuser	Type:
Sandblasted on first surface	Note:
Physical & Mechanical Properties	
±0.25	Dimensional Tolerance (mm):
12.50 x 12.50	Dimensions (mm):

Cut	Edges:
120	Grit: ☐
1.60	Thickness (mm):
12.50	Width (mm):
12.50	Length (mm):


Optical Properties	
Uncoated	Coating:
Float Glass	Substrate: ☐
350 - 2000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
 - Low Scatter Loss
 - Evenly Ground Surface for Even Diffusion
 - **Fused Silica Substrates** Available
- Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.
- Can't find what you need? Get a quick [custom quote](#).

Technical Information



Quote Your Size

Compatible Mounts