

[See all 36 Products in Family](#)

## 12.5mm Dia., 2mm Thick, Uncoated, Suprasil Window



Suprasil® Windows

Stock **#15-469** **20+ In Stock**

1  MRP ₹13,621

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-5	₹13,621 each
Qty 6-25	₹10,896 each
Qty 26-49	₹10,190 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Protective Window **Type:**

Glass **Type of Window:**

#### Physical & Mechanical Properties

Clear Aperture CA (mm):

11.25	<b>Diameter (mm):</b>
12.50 +0.00/-0.10	
	<b>Thickness (mm):</b>
2.00 ±0.10	
	<b>Bevel:</b>
Protective as needed	
	<b>Clear Aperture (%):</b>
90	
	<b>Edges:</b>
Fine Ground	
	<b>Parallelism (arcsec):</b>
<5	
	<b>Poisson's Ratio:</b>
0.17	
	<b>Young's Modulus (GPa):</b>
70	
	<b>Knoop Hardness (kg/mm<sup>2</sup>):</b>
591.00	

## Optical Properties

	<b>Coating:</b>
Uncoated	
	<b>Substrate:</b> <input type="checkbox"/>
Suprasil® 300	
	<b>Index of Refraction (n<sub>d</sub>):</b>
1.459	
	<b>Surface Quality:</b>
10-5	
	<b>Transmitted Wavefront, P-V:</b>
λ/10	
	<b>Abbe Number (v<sub>d</sub>):</b>
67.8	
	<b>Wavelength Range (nm):</b>
200 - 3500	

## Material Properties

	<b>Density (g/cm<sup>3</sup>):</b>
2.20	
	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
0.51 (0 to +100°C)	
0.58 (0 to +200°C)	

## Regulatory Compliance

	<b>Certificate of Conformance:</b>
<a href="#">View</a>	
	<b>Country of Origin:</b>
Vietnam	
	<b>Imported By:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

## Product Details

- High Transmission from 200 to 3500nm
- <1 ppm OH Content for Minimal Absorption Losses
- 10-5 Surface Quality and up to λ/10 TWD

Suprasil® Windows are constructed from high purity synthetic fused silica and provide high, flat transmission from 200 to 3500nm. Suprasil has similar mechanical properties to fused silica with the added benefit of having no absorption bands in the visible or infrared spectra, resulting in no transmission loss between 1400 - 2700nm. Compared to Infrasil®, Suprasil has lower absorption with a <1 ppm OH content, causing negligible increase in temperature from bulk absorption when used with high powered lasers. Suprasil Windows are ideal for laser material processing, medical laser applications, or applications using Nd:doped or 2 micron lasers.

## Technical Information



## Compatible Mounts

---