

TECHSPEC® 12.5mm Dia 785nm 0°, Laser Diode Mirror



Stock **#63-147** CLEARANCE 10 TO 12 DAYS

-

1

+

₹3,475.65

ADD TO CART

Qty 1+
₹3,475.65

Volume Pricing
Request Quote

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):
>90

Back Surface:
Ground

Reflection at DWL (%) : 99.8
Coating Specification : R _{abs} >99.8% @ 785nm R _{avg} >98% @ 730 - 840nm
Wavelength Range (nm) : 730 - 840
Surface Flatness (P-V) : λ/10
Coating Type : Dielectric
Coating : Dielectric Mirror (730-840nm)
Design Wavelength DWL (nm) : 785
Diameter (mm) : 12.50 +0.0/-0.2
Thickness (mm) : 6.00 ±0.2
Angle of Incidence (°) : 0
Substrate : ☐ Fused Silica (Corning 7980)

Regulatory Compliance

RoHS : Compliant
Reach 224 : Compliant
Certificate of Conformance : View