

[See all 4 Products in Family](#)

12.5mm Dia., 1.1mm Thick, Uncoated, SCHOTT Xensation® Chemically Strengthened Window

See More by [SCHOTT Optical Components](#)



Stock #17-260 **20+ In Stock**

- 1 + MRP ₹2,119

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹2,119 each
Qty 6-25	₹1,614 each
Qty 26-99	₹1,514 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**
Glass **Type of Window:**

Physical & Mechanical Properties

11.25	Clear Aperture CA (mm):
12.50 ±0.127	Diameter (mm):
1.10 Nominal	Thickness (mm):
Protective as needed	Bevel:
90	Clear Aperture (%):
Fine Ground	Edges:
0.21	Poisson's Ratio:
74	Young's Modulus (GPa):
639.00	Knoop Hardness (kg/mm²):

Optical Properties

Uncoated	Coating:
SCHOTT Xensation®	Substrate: <input type="checkbox"/>
1.51	Index of Refraction (n_d):
80-50	Surface Quality:
380 - 840	Wavelength Range (nm):

Material Properties

2.48	Density (g/cm³):
615	Transformation Temperature (°C):
8.8 (+20 to +300°C)	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Highly Resistant to Breakage and Surface Scratches
- Microfloat Manufacturing Process
- Ideal for Capacitive Touch Technologies
- [TECHSPEC® Gorilla® Glass Windows](#) and [Dragontrail™ Chemically Strengthened Windows](#) Also Available

SCHOTT Xensation® Chemically Strengthened Windows provide hardened substrates with outstanding resistance to breakage and scratches. These windows feature a Knoop Hardness of 639, making them harder and tougher than soda lime float substrates. Typical compressive stress (CS) and depth of layer (DoL) values are evenly balanced to deliver outstanding mechanical reliability. SCHOTT Xensation® Chemically Strengthened Windows feature a high transmittance between 390 – 840nm and are widely used as protective cover glass for capacitive touch technologies display devices. Custom coatings and sizes are available for volume OEM applications.

Quote Your Size