

TECHSPEC® 12.5mm Dia. x 20mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-322-INK** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹8,352.00**

ADD TO CART

Qty 1-5
₹8,352.00
Qty 6+
₹6,677.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 ±0.025

Effective Focal Length EFL (mm):
20.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 16.45
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 10.50 ±0.10
Center Thickness CT 1 (mm): 5.25 ±0.05
Center Thickness CT 2 (mm): 5.25 ±0.05
Radius R₁ (mm): 13.98
Radius R₂ (mm): -9.35
Radius R₃ (mm): -76.14
Edge Thickness ET (mm): 4.62
Substrate: ☐ S-BAH11 / N-SF10
Surface Quality: 40-20
f/#: 1.6
Numerical Aperture NA: 0.31
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View