

TECHSPEC® 12.5mm Dia. x 50mm FL, VIS 0° Coated, Achromatic Lens



Stock **#47-667** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹7,047.00**

ADD TO CART

Qty 1-5
₹7,047.00
Qty 6+
₹5,633.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):
50.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 47.61
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 5.00 ±0.10
Center Thickness CT 1 (mm): 3.50 ±0.05
Center Thickness CT 2 (mm): 1.50 ±0.05
Radius R₁ (mm): 30.73
Radius R₂ (mm): -22.32
Radius R₃ (mm): -64.75
Edge Thickness ET (mm): 4.06
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 4.00
Numerical Aperture NA: 0.13
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant