

[See all 5 Products in Family](#)

TECHSPEC® 12.5mm Dia 405nm 45°, Laser Diode Mirror



Stock #63-138 **20+ In Stock**

MRP ₹11,603

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹11,603 each
Qty 6-25	₹10,493 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

>90 **Clear Aperture (%):**

Back Surface:

Ground	
12.50 +0.0/-0.2	Diameter (mm):
6.00 ±0.2	Thickness (mm):
Optical Properties	
10-5	Surface Quality:
99.8	Reflection at DWL (%):
R _{abs} >99.8% @ 405nm R _{avg} >98% @ 375 - 435nm	Coating Specification:
375 - 435	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):
Dielectric	Coating Type:
Dielectric Mirror (375-435nm)	Coating:
405	Design Wavelength DWL (nm):
45	Angle of Incidence (°):
Fused Silica (Coming 7980)	Substrate: <input type="checkbox"/>

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details









- >99.8% Reflectivity at Design Wavelengths
- Excellent Broadband Performance for Range of Wavelengths
- Designed for Common Diode Lasers

TECHSPEC® Diode Laser Line Mirrors are designed to offer high reflection for the most common diode laser wavelengths. Designed for a 0° or 45° angle of incidence, these mirrors are ideal for beam-steering and folding applications.

Our line of [TECHSPEC® laser line mirrors](#) are specially designed for even the most demanding laser applications. Combining laser-quality substrates of up to 10-5 surface quality, with a dense reflective coating, and a damage threshold specific to the laser type and wavelength, these mirrors are ideal for a wide range of applications requiring precision reflectivity and incredible durability. All TECHSPEC® laser line mirrors are designed to minimize scatter loss and to be easily mounted into any optical system.



Technical Information



Typical Reflectivity Curves



Compatible Mounts