

TECHSPEC[®] 12.5mm Dia. 532nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC[®] Nd:YAG Laser Line Mirrors

Stock #88-529 10 TO 12 DAYS

-

1

+

₹12,528.00

ADD TO CART

Qty 1-5
₹12,528.00
Qty 6+
₹11,049.00
Volume Pricing
Request Quote

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):

>90
Back Surface: Ground
Reflection at DWL (%): 99.9
Coating Specification: R _{abs} >99.8% @ 532nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (532nm)
Design Wavelength DWL (nm): 532
Diameter (mm): 12.50 +0.0/-0.2
Thickness (mm): 6.00 ±0.2
Angle of Incidence (°): 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 10 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View