


TECHSPEC® 125mm Diameter Uncoated, Calcium Fluoride Window



TECHSPEC Calcium Fluoride (CaF₂) Windows

Stock #17-606 [CONTACT US](#)

1

MRP ₹3,67,745

Price inclusive of all taxes

[ADD TO CART](#)

Volume Pricing	
Qty 1-10	₹3,67,745 each
Qty 11-25	₹3,24,866 each
Qty 26-49	₹3,06,706 each
Need More?	Request Quote

Product Downloads

- STEP:step
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Type: Protective Window	Type of Window: Crystal
--------------------------------	--------------------------------

Physical & Mechanical Properties

Clear Aperture CA (mm): 112.50	Diameter (mm): 125.00 +0.0/-0.1
Thickness (mm): 6.00 ±0.10	Parallelism (arcmin): <3
Bevel: Protective as needed	Clear Aperture (%): 90
Edges: Fine Ground	Poisson's Ratio: 0.26
Young's Modulus (GPa): 75.8	Knoop Hardness (kg/mm²): 158.30

Optical Properties

Coating: Uncoated	Substrate: ① Calcium Fluoride (CaF ₂) Vacuum UV Grade
Index of Refraction (n_d): 1.434	Surface Quality: 60-40
Abbe Number (v_d): 94.99	Axis Orientation: Random
Wavelength Range (nm): 200 - 7000	Surface Flatness (P-V): 1λ

Material Properties

Density (g/cm³): 3.18	Coefficient of Thermal: 18.85
---	--------------------------------------

Regulatory Compliance

RoHS 2015: Compliant	Reach 219: Compliant
Certificate of Conformance: View	
Country of Origin: United States	Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Low Absorption, High Transmission UV Grade Calcium Fluoride
- Low Index of Refraction
- AR Coatings Spanning 250 - 5000nm Available
- **Calcium Fluoride (CaF₂) Wedged Windows** also Available

TECHSPEC® Calcium Fluoride (CaF₂) Windows offer a low index of refraction, providing high transmission from 200 - 7000nm when used uncoated. To further increase transmission and reduce back reflections, a variety of AR coatings are available spanning wavelength regions from the Ultra-Violet (UV) to the Mid-Wave Infrared (MWIR). The high bulk damage threshold of calcium fluoride coupled with its low absorption makes it a popular choice for use with laser systems, including excimer lasers. TECHSPEC® Calcium Fluoride (CaF₂) Windows are ideal for use as protective windows for gas detectors operating in the Vacuum UV (VUV) and MWIR, UV spectroscopy systems, cryogenically cooled thermal imaging systems, and as substrates for coatings requiring wideband substrate transmission.

Note: Calcium fluoride is a relatively soft optical material and is more susceptible to scratches than typical glass windows. Calcium fluoride is also susceptible to thermal shock.

Technical Information


Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.




Component Handling Tools


Related Products



Calcium Fluoride Optics



ISP Optics Calcium Fluoride (CaF₂) Wedged Windows



1λ UV Fused Silica Windows




Magnesium Fluoride (MgF₂) Windows


Resources

Media Type

- Application Note
- Scientific Paper
- Video
- Glossary
- Technical Tool
- FAQ




APPLICATION NOTE
Anti-Reflection (AR) Coatings



APPLICATION NOTE
An Introduction to Optical Coatings

SPIE.


SCIENTIFIC PAPER
Advantages of using engineered chalcogenide...



VIDEO
Infrared Light



GLOSSARY
Short Wave Infrared (SWIR)



TECHNICAL TOOL
Beam Displacement Calculator

[View More](#)

;