


TECHSPEC[®] 12.5mm Dia x 10mm FL Acylinder Lens, MgF₂ Coated



TECHSPEC Acylinder Lenses

Stock **#86-034** **3 In Stock**

-

1

+

₹50,603

ADD TO CART

Volume Pricing	
Qty 1-5	₹50,603 each
Qty 6-25	₹40,482 each
Qty 26-49	₹37,368 each
Need More?	Request Quote


Product Downloads

General	
Acylinder Lens	Type:
Physical & Mechanical Properties	
12.50 +0.0/-0.1	Diameter (mm):
6.00	Center Thickness CT (mm):


±0.1	Center Thickness Tolerance (mm):
90.00	Clear Aperture (%):
2.8	Edge Thickness ET (mm):
Optical Properties	
10.00	Effective Focal Length EFL (mm):
N-SF5	Substrate: ☐
0.8	f/#:
0.63	Numerical Aperture NA:
MgF ₂ (400-700nm)	Coating:
400 - 700	Wavelength Range (nm):
6.4	Back Focal Length BFL (mm):
R _{avg} ≤1.75% @400 - 700nm	Coating Specification:
587.6	Focal Length Specification Wavelength (nm):
1.0	Surface Accuracy, RMS (μm):
60-40	Surface Quality:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Diffraction Limited Design
 - Ideal for Creating Thin Line Profiles of Monochromatic Light Sources
 - Focus Light in Single Dimension
- TECHSPEC® Acylinder Lenses are similar to aspheric lenses in that they provide diffraction-limited focusing performance in only one dimension. By reducing spherical aberration along the focusing axis, TECHSPEC® Acylinder Lenses are ideal for creating thin line profiles. Compared to standard cylinder lenses, TECHSPEC® Acylinder Lenses also dramatically reduce the spot size of monochromatic light sources to provide sharp, thin lines.



Technical Information



Coating Curves

;