

TECHSPEC[®] 12.5mm Dia. x 20mm FL, VIS 0° Coated, Achromatic Lens



Stock **#47-661** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹7,047.00

ADD TO CART

Qty 1-5
₹7,047.00
Qty 6+
₹5,633.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):
20.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 16.45
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 11.50
Centering (arcmin) : <1
Center Thickness CT (mm) : 6.35 ±0.10
Center Thickness CT 1 (mm) : 5.25 ±0.05
Center Thickness CT 2 (mm) : 1.10 ±0.05
Radius R₁ (mm) : 13.98
Radius R₂ (mm) : -9.35
Radius R₃ (mm) : -76.14
Edge Thickness ET (mm) : 4.62
Substrate : ☐ S-BAH11 / N-SF10
Surface Quality : 40-20
f/# : 1.6
Numerical Aperture NA : 0.31
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View