

TECHSPEC[®] 12.5mm FL f/4, Blue Series M12 Lens



12.5mm FL Blue Series M12 Lens



Stock **#69-264** 20+ In Stock

-

1

+

₹7,395

ADD TO CART

Volume Pricing	
Qty 1+	₹7,395 each
Need More?	Request Quote

Product Downloads

General	
Blue Series	Series:
M12 Imaging Lens	Type:
No	IR Cut Filter:
High Performance M12 Lens	Imaging Lens Type:

Physical & Mechanical Properties	
Fixed	Iris Option:
22.90	Length (mm):
15	Maximum Diameter (mm):
15	Outer Diameter (mm):
6	Weight (g):
Optical Properties	
28.9°	Horizontal Field of View @ Max Sensor Format:
Horizontal: 78.1mm - 28.9° Vertical: 58.5mm - 21.8° Diagonal: 97.7mm - 35.7°	Field of View at Max Sensor Format:
78.0mm - 28.8°	Horizontal Field of View, 1/2" Sensor:
70.6mm - 26.2°	Horizontal Field of View, 1/2.5" Sensor:
58.4mm - 21.8°	Horizontal Field of View, 1/3" Sensor:
43.8mm - 16.4°	Horizontal Field of View, 1/4" Sensor:
8.00	Maximum Image Circle (mm):
0.0095	Numerical Aperture NA, Object Side:
5(5)	Number of Elements (Groups):
400 - 700	Wavelength Range (nm):
12.50	Focal Length FL (mm):
150 - ∞	Working Distance (mm):
f/4	Aperture (f/#):
-0.36 @ Full Field	Distortion (%):
10.1 - 9.7	Back Focal Length BFL (mm):
N/4 MgF ₂ @ 550nm	Coating Specification:
10.87	Entrance Pupil Position (mm):
10.14	Object Space Principal Plane (mm):
-3.01	Image Space Principal Plane (mm):
-0.36	Maximum Distortion (%):
-2.33	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:
Sensor	
1/2"	Maximum Sensor Format:
1.40	Pixel Size (µm):
Threading & Mounting	
N/A	Filter Thread:
S-Mount (M12 x 0.5)	Mount:
Regulatory Compliance	

RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	

Reach 247:	
Compliant	

Product Details

- Up to 1/2", S-Mount Lens
- Up to 5 MegaPixels, 1.4µm Pixel Size Sensors
- High Resolution Board Camera Lens Optimized for Close WD
- 2mm to 35mm Focal Length
- [Ruggedized Designs](#) Also Available


TECHSPEC® Blue Series M12 Lenses feature high resolution performance, along with the same great versatility of our [TECHSPEC® Green Series M12 Lenses](#). Each lens consists of several precision glass elements mounted in a compact, aluminum housing. These lenses can connect to C-Mount cameras using the M12 x0.5 Adapter for C-Mount Cameras ([#53-675](#)) or the M12 x0.5 C-Mount Adapter with Rubber O-Ring ([#59-241](#)) for vibration-sensitive environments. TECHSPEC® Blue Series M12 Lenses are ideal for automotive, industrial, and medical imaging application. Prescription data is available by submitting a [Request for Prescription Form](#).

Note: Compatible [TECHSPEC® M12 Imaging Lens Accessories](#) available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- Blue Series M12 Lenses: High resolution finite conjugate designs optimized for machine vision working distances.
- [Rugged Blue Series M12 Lenses](#): [Stabilized ruggedization](#) versions of our Blue Series M12 Lenses, utilizing the same optics.
- [Green Series M12 Lenses](#): Finite conjugate designs optimized for machine vision working distances.
- [Red Series M12 Lenses](#): Infinite conjugate designs optimized for high resolution performance out to infinity.
- [HEO Series M12 Lenses](#): Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- [Liquid Lens M12 Lenses](#): Integrated liquid lens for fast electronic focus.


Technical Information




#69-264, 12.5mm FL f/4, Blue Series M12 Lens, Distortion Plot



#69-264, 12.5mm FL f/4, Blue Series M12 Lens, Relative Illumination Plot




#69-264, 12.5mm FL f/4, Blue Series M12 Lens, Working Distance versus Field of View Plot



#69-264, 12.5mm FL f/4, Blue Series M12 Lens, Modulated Transfer Function (MTF) Plot, 150mm Working Distance, f4



#69-264, 12.5mm FL f/4, Blue Series M12 Lens, Depth of Field Plot, 150mm Working Distance, f4



#69-264, 12.5mm FL f/4, Blue Series M12 Lens, Modulated Transfer Function (MTF) Plot, 400mm Working Distance, f4



#69-264, 12.5mm FL f/4, Blue Series M12 Lens, Depth of Field Plot, 400mm Working Distance, f4

Focal Length	A	B	C*	D
2.0mm	18.0mm	21.7mm	2.26mm	4.75mm
3.0mm	14.0mm	17.1mm	4.8 - 4.7mm	5.8mm
4.0mm	14.0mm	19.7mm	6.1 - 6.0mm	4.4mm
5.0mm	14.0mm	14.6mm	4.0 - 3.9mm	3.7mm
6.0mm	14.0mm	14.1mm	6.9 - 6.8mm	4.5mm
8.0mm	14.0mm	12.3mm	8.8 - 8.6mm	3.7mm
10.0mm	14.0mm	17.0mm	6.6 - 6.3mm	3.7mm

12.5mm	15.0mm	22.9mm	10.1 - 9.7mm	4.8mm
17.5mm	14.0mm	20.7mm	5.8 - 4.9mm	7.6mm
25.0mm	18.0mm	30.0mm	8.5 - 6.5mm	11.5mm
35.0mm	18.0mm	29.5mm	18.72 - 14.0mm	14.5mm



*Specified for Optimized Working Distance of 150 - 250mm.