

TECHSPEC[®] 12.5mm Dia. x 90mm FL, VIS 0° Coated, Achromatic Lens



Stock **#47-671** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹7,047.00

ADD TO CART

Qty 1-5
₹7,047.00
Qty 6+
₹5,633.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):
90.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 88.47
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 3.58 ±0.10
Center Thickness CT 1 (mm): 1.98 ±0.05
Center Thickness CT 2 (mm): 1.60 ±0.05
Radius R₁ (mm): 55.80
Radius R₂ (mm): -40.17
Radius R₃ (mm): -116.32
Edge Thickness ET (mm): 3.06
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 7.2
Numerical Aperture NA: 0.07
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View