

[See all 24 Products in Family](#)

**TECHSPEC® 12.5mm Dia x -15mm FL Negative Doublet Lens MgF<sub>2</sub> Coated**



Stock **#48-350 6 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹9,333

ⓘ Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹9,333 each
Qty 6-25	₹7,466 each
Qty 26-49	₹7,012 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Negative Achromatic Lens **Type:**

**Physical & Mechanical Properties**

12.50 +0.0/-0.025 **Diameter (mm):**

**Clear Aperture CA (mm):**

11.50

<1 **Centering (arcmin):**

6.00 ±0.10 **Center Thickness CT (mm):**

2.00 ±0.05 **Center Thickness CT 1 (mm):**

4.00 ±0.05 **Center Thickness CT 2 (mm):**

8.04 **Edge Thickness ET (mm):**

Protective as needed **Bevel:**

### Optical Properties

-15.00 **Effective Focal Length EFL (mm):**

±1 **Focal Length Tolerance (%):**

-18.08 **Back Focal Length BFL (mm):**

587.6 **Focal Length Specification Wavelength (nm):**

-10.62 **Radius R<sub>1</sub> (mm):**

8.63 **Radius R<sub>2</sub> (mm):**

81.12 **Radius R<sub>3</sub> (mm):**

**Substrate:**

**N-BAF10 / N-SF10**

40-20 **Surface Quality:**

1.25 **f#:**

0.40 **Numerical Aperture NA:**

MgF<sub>2</sub> (400-700nm) **Coating:**

**Coating Specification:**  
R<sub>avg</sub> ≤1.75% @ 400 - 700nm

1.5λ **Power (P-V) @ 632.8nm:**

λ/4 **Irregularity (P-V) @ 632.8nm:**

400 - 700 **Wavelength Range (nm):**

### Regulatory Compliance

**RoHS 2015:**  
**Compliant**

**Certificate of Conformance:**  
**View**

**Reach 250:**  
**Compliant**

**Country of Origin:**  
Japan

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Magnesium Fluoride (MgF<sub>2</sub>) Coating
- Used to Extend Focal Length
- [Broadband AR Coated Negative Achromatic Lenses](#) Also Available

TECHSPEC® MgF<sub>2</sub> Coated Negative Achromatic Lenses consist of two optical elements cemented together. Negative doublet lenses are corrected for color and on-axis aberrations. TECHSPEC MgF<sub>2</sub> Coated Negative Achromatic Lenses are used predominantly as Barlow lenses to extend focal lengths. These lenses are often combined with positive achromatic mirror systems and imaging lenses.

## Technical Information



## Coating Curves

## Compatible Mounts