

12.5mm Square IR Cut-Off Filter



Stock **#55-235** [CONTACT US](#)

-

1

+

₹3,075

ADD TO CART

Volume Pricing	
Qty 1-24	₹3,075 each
Qty 25-49	₹2,764 each
Need More?	Request Quote

Product Downloads

General

Type:

IR Cut-Off Filter

Physical & Mechanical Properties

Dimensions (mm):

12.5 x 12.5

Length (mm):

12.50

Thickness (mm):

1.10 ±0.25

12.50	Width (mm):
±0.25	Dimensional Tolerance (mm):
≥90	Clear Aperture (%):

Seamed	Edges:
--------	--------

Optical Properties

710.00	Cut-Off Wavelength (nm):
BOROFLOAT®	Substrate: ☐

Traditional Coated	Coating:
1.472	Index of Refraction (n _d):

80-50	Surface Quality:
Coating Specification: Surface 1: T=50% @ 710±30nm, T _{avg} >85% @ 480 - 680nm, T _{avg} <10% @ 740 - 1200nm Surface 2: N/4 MgF ₂	

480 - 1200	Wavelength Range (nm):
------------	------------------------

Environmental & Durability Factors

<250	Operating Temperature (°C):
------	-----------------------------

Regulatory Compliance


Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- 710nm Cut-Off Wavelength
- Circular and Rectangular Options
- Various Sizes Available

IR Cut-Off Filters are ideal for eliminating illumination beyond the visible spectrum in many visual and detector-based applications. These filters feature a 710nm cut-off wavelength. IR Cut-Off Filters are traditionally coated and have a BOROFLOAT® substrate. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass. IR Cut-Off Filters are available in circular and rectangular versions with various sizes for each.

Technical Information



Quote Your Size

Compatible Mounts

;