

## 12.5mm Diameter 220 Grit Ground Glass Diffuser



Stock #62-616 **20+ In Stock**

MRP ₹1,438

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹1,438 each
Qty 11+	₹1,312 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Ground Glass Diffuser **Type:**

Sandblasted on first surface **Note:**

#### Physical & Mechanical Properties

12.50 ±0.25 **Diameter (mm):**

**Edges:**

Ground

Grit:   
Thickness (mm):  
1.60

### Optical Properties

Coating:  
Uncoated  
Substrate:   
Wavelength Range (nm):  
350 - 2000

### Regulatory Compliance

RoHS 2015:  
[Compliant](#)  
Certificate of Conformance:  
[View](#)

Reach 250:  
[Compliant](#)

Country of Origin:  
United States

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



[Quote Your Size](#)

[Compatible Mounts](#)