

12.5mm Diameter Mid-Wave Infrared Polarizer



Stock **#85-262** **5 In Stock**

-

1

+

MRP ₹82,226

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹82,226 each
Qty 6+	₹65,579 each
Need More?	Request Quote

Product Downloads

General

Type:

Linear Polarizer

Physical & Mechanical Properties

Clear Aperture CA (mm):

8.1

Diameter (mm):

12.50

Thickness (mm):

5.00	
Nanoparticle	Construction:
Optical Properties	
±20	Angle of Incidence (°):
>1,000:1 (1500-5000nm) >10,000:1 (2000-4500nm)	Extinction Ratio:
Soda Lime Float Glass	Substrate: □
60-40	Surface Quality:
35 (1500-5000nm) 65 (2000-4500nm)	Transmission (%):
<3λper 10mm	Transmitted Wavefront, P-V:
<1	Beam Deviation (arcmin):
±2	Polarization Axis Mark (%):
1500 - 5000	Wavelength Range (nm):
1 W/cm² (Continuous Block) 5 W/cm² (Continuous Pass)	Damage Threshold, By Design: □
Environmental & Durability Factors	
-20 to +120	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
Germany	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- 1.5 – 5µm Wavelength Range
- Mounted for Easy Handling and System Integration
- Highly Durable Soda Lime Substrate

Featuring high contrast ratios and transmittances, Mid-Wave Infrared (MMIR) Polarizers are designed for applications operating in the 1.5 – 5µm wavelength range. Ideal for harsh environments, each MMIR polarizer is constructed of a dichroic glass substrate which provides a high resistance to UV radiation and chemicals, as well as an operating temperature of up to 400°C.