


TECHSPEC® 12.7 x 12.7mm 266nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#39-581** 10 TO 12 DAYS



1



₹11,919.00

ADD TO CART

Qty 1-5
₹11,919.00
Qty 6+
₹10,527.00
Volume Pricing
Request Quote

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):

85
Back Surface: Commercial Polish
Reflection at DWL (%): 99.5
Coating Specification: R _{abs} >99.5% @ 266nm R _{avg} >99.5% @ 263 - 268nm
Wavelength Range (nm): 263 - 268
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (263-268nm)
Design Wavelength DWL (nm): 266
Dimensions (mm): 12.7 x 12.7 +0.00/-0.10
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 2.5 J/cm² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View