

TECHSPEC® 12.75mm Dia., 1mm Thick, Uncoated, Sapphire Window



Stock #43-631 **20+ In Stock**

1 **MRP ₹5,386**

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-24	₹5,386 each
Qty 25-50	₹4,136 each
Qty 51-99	₹4,039 each
Need More?	Request Quote

Product Downloads

- STEP:step
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Type: Protective Window	Type of Window: Crystal
--------------------------------	--------------------------------

Physical & Mechanical Properties

Clear Aperture CA (mm): 11.48	Diameter (mm): 12.75 ±0.15
Thickness (mm): 1.00 ±0.10	Parallelism (arcmin): ≤3.5
Bevel: Protective as needed	Clear Aperture (%): ≥90
Edges: Fine Ground	Poisson's Ratio: 0.27
Young's Modulus (GPa): 435	Knoop Hardness (kg/mm²): 1,900.00

Optical Properties

Coating: Uncoated	Substrate: ^① Sapphire (Al ₂ O ₃)
Index of Refraction (n_d): 1.77	Surface Quality: 80-50
Abbe Number (v_d): 72.24	Surface Roughness (µm): 0.1 per Inch
Birefringence (n_o-n_e): 0.008 for Visible Light Orthogonal to Optical Axis	Axis Orientation: Random
Wavelength Range (nm): 330 - 5500	Surface Flatness (P-V): 2λ (typical)

Material Properties

Density (g/cm³): 3.97

Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 5.4 (Parallel to C-Axis)
4.3 (Perpendicular to C-Axis)

Regulatory Compliance

RoHS 2015: [Compliant](#)

Certificate of Conformance: [View](#)

Reach 247: [Compliant](#)

Country of Origin: Switzerland

Imported By: Edmund Optics India Private Limited
267, Greystone Building,
Second Floor,
6th Cross Rd,
Binnamangala,
Stage 1,
Indiranagar,
Bengaluru,
Karnataka,
India 560038
Phone: +91-80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Features Extreme Surface Hardness Chemical Resistance
- Transmits Wavelengths Ranging From UV to Mid-Infrared
- Thinner and Stronger than Standard Glass Windows
- Anti-Reflection Coating Options Covering 350 - 5000nm Available

TECHSPEC® Sapphire Windows are manufactured from single crystal sapphire, making them ideal for demanding applications (such as laser systems) because of their extreme surface hardness, high thermal conductivity, high dielectric constant and resistance to common chemical acids and alkalis. Sapphire is the second hardest crystal next to **diamond** and, because of their structural strength, sapphire windows can be made much thinner than other common windows with improved transmittance. Chemically, sapphire is single crystal aluminum oxide (Al₂O₃) and is useful in a transmission range from UV to mid-infrared or 330 - 5500nm when uncoated. TECHSPEC® Sapphire Windows are available with anti-reflection (AR) coatings to improve performance in the visible, NIR, and IR spectra with coating options covering 350 - 5000nm.

Technical Information

Related Products



Cage System Optical Lens Mounts



C, S, and T-Mount Circular Optic Mounts



PUROSOL™ Optical Cleaner

Frequently Purchased Together




#27-402 - 12.5mm Diameter, 4-6λ Mirror
₹1,918

#30-120 - 15mm Dia x 25.4mm EFL Hastings Triplet Achromatic Lens
₹15,235

#32-317 - 12.5mm Dia. x 50mm FL, MgF₂ Coated, Achromatic Doublet Lens
₹8,677

#00-736 - 7.75" x 10.75" Sheets, Industrial Grade Lens Tissue
₹7,434

Compatible Mounts


	Title	Type	Compare	Stock Number	Price	Buy
	5.0 - 25.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-529	₹10,291 Request Quote	20+ In Stock <input type="text" value="1"/>
	7.0 - 40.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-676	₹10,694 Request Quote	2 In Stock <input type="text" value="1"/>
	10.0 - 60.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-530	₹10,896 Request Quote	CONTACT US <input type="text" value="1"/>
	7.0 - 67.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-669	₹11,703 Request Quote	6 In Stock <input type="text" value="1"/>
	8.0 - 118.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-666	₹12,107 Request Quote	10 In Stock <input type="text" value="1"/>
	4.0 - 36.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-077	₹15,840 Request Quote	6 In Stock <input type="text" value="1"/>
	5.0 - 100.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-078	₹41,365 Request Quote	CONTACT US <input type="text" value="1"/>


Resources


Media Type

- Application Note
- Technical Tool
- Video
- Glossary
- FAQ

 APPLICATION NOTE
**Anti-Reflection
(AR) Coatings**

 APPLICATION NOTE
**An
Introduction to
Optical
Coatings**

 TECHNICAL TOOL
**Beam
Displacement
Calculator**

 APPLICATION NOTE
**Understanding
Optical
Windows**

 VIDEO
**Optical
Windows
Review**

 APPLICATION NOTE
Optical Glass

[View More](#)