

12.5mm FL SWIR Series Fixed Focal Length Lens



Stock **#83-816** **9 In Stock**

-

1

+

₹1,93,050

ADD TO CART

Volume Pricing	
Qty 1+	₹1,93,050 each
Need More?	Request Quote

Product Downloads

General

1" SWIR Series Fixed Focal Length Lenses	Series:
Fixed Focal Length Lens	Type:

Physical & Mechanical Properties

Variable	Iris Option:
52.00	Length (mm):

Maximum Diameter (mm):


42.0	
42	Outer Diameter (mm):
160	Weight (g):
Optical Properties	
300.00	Field of View @ Min Working Distance (mm):
55.6°	Horizontal Field of View, 1" Sensor:
16.00	Maximum Image Circle (mm):
12.50	Focal Length FL (mm):
300 - ∞	Working Distance (mm):
f/1.4 - f/16	Aperture (f/#):
<-2.0	Distortion (%):
-1.5	Maximum Distortion (%):
SWIR	Lens Wavelength Range:
Sensor	
1"	Maximum Sensor Format:
4.50	Pixel Size (µm):
Threading & Mounting	
M35.5 x 0.50	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- 1", C-Mount Lens
- Spectral Range of 800 - 2000nm for InGaAs SWIR Sensors
- 8mm to 50mm Focal Lengths

Short Wave Fixed Focal Length Lenses are the best choice for use with SWIR cameras. The SWIR spectrum is an ideal choice for a variety of applications, including solar cell inspection, security, and biomedical imaging. When utilized in conjunction with a SWIR camera, these lenses will permit imaging through silicon, imaging outdoors without additional illumination, detecting bruising on fruit, and a host of additional infrared applications.

Technical Information



;