

TECHSPEC[®] 12.5mm H x 25mm L x 20mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#68-031** 20+ In Stock

-

1

+

₹4,982

ADD TO CART

Volume Pricing	
Qty 1-5	₹4,982 each
Qty 6-25	₹4,476 each
Qty 26-49	₹4,243 each
Need More?	Request Quote

Product Downloads

General

Cylinder Lens, Plano-Convex

Type:

Physical & Mechanical Properties

3.60Center Thickness CT (mm):

±0.1Center Thickness Tolerance (mm):

+0.0/-0.2	Dimensional Tolerance (mm):
12.5 x 25.0	Dimensions (mm):
1.50	Edge Thickness ET (mm):
Optical Properties	
20.00	Effective Focal Length EFL (mm):
N-BK7	Substrate: ☐
1.6	f/#:
0.31	Numerical Aperture NA:
Uncoated	Coating:
350 - 2200	Wavelength Range (nm):
17.63	Back Focal Length BFL (mm):
±3	Focal Length Tolerance (%):
10.34	Radius R ₁ (mm):
60-40	Surface Quality:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	REACH 201:
View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- N-BK7 Substrate for Broadband Performance
- Cost-Effective for OEM Integration
- Multiple Coating Options Available

TECHSPEC® Illumination Grade PCX Cylinder Lenses are similar to Plano-Convex (PCX) lenses in profile, but include a portion of a cylinder instead of a sphere. These lenses focus light in one dimension and can transform a point of light into a line. TECHSPEC® Illumination Grade PCX Cylinder Lenses are available in circular and rectangular versions, along with multiple coating options. Cylinder lenses are ideal for line projection in machine vision applications or guidance systems.

Note: For negative focal length cylinder lenses, see our [TECHSPEC® Illumination Grade PCV Cylinder Lenses](#).


LASER OPTICS


MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information





PCX Rectangular

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
