

12.7mm Dia., 1064nm, $\lambda/2$ High Energy Waveplate



High Energy Quartz Waveplates

Stock **#25-453** **1 In Stock**

-

1

+

₹43,985

ADD TO CART

Volume Pricing	
Qty 1-10	₹43,985 each
Qty 11+	₹37,757 each
Need More?	Request Quote

Product Downloads

General

High Energy Waveplate

Type:

Physical & Mechanical Properties

8.0

Clear Aperture CA (mm):

12.70

Diameter (mm):

Dimensional Tolerance (mm):

+0/-0.2	
	Construction: Optically Bonded on UVFS (C7980) Substrate
	Parallelism (arcsec): <3
Optical Properties	
Coating: R _{avg} <0.3%	
Design Wavelength DWL (nm): 1064	
Substrate: ☐ Crystalline Quartz	
Retardance: λ/2	
Surface Quality: 20-10	
Transmitted Wavefront, P-V: <λ/10 @ 632.8nm	
Retardance Tolerance: λ/300 @ 20°C	
Damage Threshold, By Design: ☐ >20 J/cm ² @ 1064nm, 10ns, 10Hz	
Retardance Order: 1	
Threading & Mounting	
Mount Thickness (mm): 6 ±0.2	
Regulatory Compliance	
RoHS 2015: Compliant	
Certificate of Conformance: View	
Reach 247: Compliant	
Country of Origin: Lithuania	
Imported By: Edmund Optics India Private Limited	

Product Details

- Damage Threshold up to >20 J/cm² @ 1064nm
- λ/4 and λ/2 Retardance
- Black Anodized Aluminum Mount
- UV to NIR Design Wavelengths Available

High Energy Quartz Waveplates are available in both λ/4 and λ/2 retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to >20 J/cm² at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.