


[See all 4 Products in Family](#)

12.7mm Dia., 2mm Thick, Uncoated, ISP Optics Silicon (Si) Window | SI-W-12-2

See More by [ISP Optics](#)



Stock **#24-624** CLEARANCE **15 In Stock**

-

1

+

₹7,391

ADD TO CART

Volume Pricing	
Qty 1+	₹7,391 each
Need More?	Request Quote

Product Downloads

General

Type:

Protective Window

Model Number:

SI-W-12-2

Physical & Mechanical Properties

Bevel:

Protective as needed

Clear Aperture (%):

85

10.79	Clear Aperture CA (mm):
12.70 +0.00/-0.13	Diameter (mm):
2.00 ±0.13	Thickness (mm):
Fine Ground	Edges:
1,150.00	Knoop Hardness (kg/mm²):
<3	Parallelism (arcmin):
0.27	Poisson's Ratio:
140	Young's Modulus (GPa):

Optical Properties

Uncoated	Coating:
3.422 @ 5µm	Index of Refraction (n _d):
Silicon (Si)	Substrate:
2λ	Surface Flatness (P-V):
40-20	Surface Quality:
1200 - 7000	Wavelength Range (nm):

Material Properties

2.55	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.33	Density (g/cm³):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited	Importer:

Product Details

- Transmission from 1.2 - 7µm
- Available Uncoated or HDAR Coated for 3 - 5µm
- Ideal for Weight Sensitive Applications

ISP Optics Silicon (Si) Windows provide transmission in the Near-Infrared (NIR) and Mid-Wave Infrared (MMIR) from 1.2 - 7µm. Silicon features a Knoop Hardness of 1150, making it harder and less brittle than Germanium. A High-Durability Anti-Reflection (HDAR) coating option increases the durability of the substrate while significantly improving transmission from 3 - 5µm, enabling use in harsh environments. ISP Optics Silicon (Si) Windows are ideal for weight-sensitive IR applications due to its low density of 2.329 g/cm³, which is half as dense as Germanium and Zinc Selenide. These windows are ideal for NIR imaging applications and are important for detection of sources radiating at a black body temperature of 700K.