


TECHSPEC<sup>®</sup> 12.5mm NIR I Coated, BBAR Coated Right Angle Prism



Stock **#84-523** 13 In Stock

-

1

+

₹10,350

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹10,350 each                  |
| Qty 6-25       | ₹8,325 each                   |
| Qty 26-49      | ₹7,920 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                             |
|----------------------------------|-----------------------------|
| Right Angle Prism                | Type:                       |
| Coating on Entrance/Exit Faces   | Note:                       |
| Physical & Mechanical Properties |                             |
| +0.00/-0.10                      | Dimensional Tolerance (mm): |

|                                                            |                                                       |
|------------------------------------------------------------|-------------------------------------------------------|
| Protective as needed                                       | Bevel:                                                |
| 90                                                         | Clear Aperture (%):                                   |
| 17.70                                                      | Length of Hypotenuse (mm):                            |
| 12.50                                                      | Length of Legs (mm):                                  |
| Optical Properties                                         |                                                       |
| ±15                                                        | Angle Tolerance (arcsec):                             |
| NIR I (600-1050nm)                                         | Coating:                                              |
| N-BK7                                                      | Substrate: <input type="checkbox"/>                   |
| 40-20                                                      | Surface Quality:                                      |
| Left-Handed                                                | Image Orientation:                                    |
| Entrance/Exit Faces: R <sub>avg</sub> ≤0.5% @ 600 - 1050nm | Coating Specification:                                |
| 90                                                         | Ray Deviation (°):                                    |
| 600 - 1050                                                 | Wavelength Range (nm):                                |
| Entrance/Exit Faces: 7 J/cm <sup>2</sup> @ 1064nm, 10ns    | Damage Threshold, By Design: <input type="checkbox"/> |
| 1.25                                                       | Power (fringes) @ 632.8nm:                            |
| 0.25                                                       | Irregularity (fringes) @ 632.8nm:                     |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 235:                  |
| Singapore                           | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |


## Product Details


- Ideal for Low Power Laser Sources
- Multiple BBAR Coatings Available
- Ray Deviation of 90°

TECHSPEC® Broadband Anti-Reflection (BBAR) Coated N-BK7 Right Angle Prisms (Leg Coated) are ideal for a range of low power laser line applications. These prisms feature tight angle tolerances and a precision N-BK7 substrate. The BBAR coating improves transmission efficiency when compared to uncoated right angle prisms. TECHSPEC® Broadband Anti-Reflection (BBAR) Coated N-BK7 Right Angle Prisms (Leg Coated) have their BBAR coating on entrance and exit faces. The prisms are available in lengths from 5 to 50mm.


Right angle prisms are generally used to bend image paths or redirect light at 90°. This produces a left-handed image and depending on the orientation of the prism, the image may be inverted or reverted. Right angle prisms can also be used in combination for image/beam displacement.

## Technical Information







Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).