

**TECHSPEC® 12.7mm Dia., 0.5mm Thick, BBAR (2000-5000nm) AR Coated Sapphire Window**



Stock **#21-017** 10 TO 12 DAYS

- 1 + **₹7,352.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-24                      |
| ₹7,352.00                     |
| Qty 25+                       |
| ₹5,873.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Abbe Number ( $v_d$ ):**  
72.24

**Axis Orientation:**  
Random

**Bevel:**  
Protective as needed

**Birefringence ( $n_o$ - $n_e$ ):**

|                                                                                                                                                         |
|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| 0.008 for Visible Light Orthogonal to Optical Axis                                                                                                      |
| <b>Clear Aperture (%)</b> :<br>≥90                                                                                                                      |
| <b>Clear Aperture CA (mm)</b> :<br>11.43                                                                                                                |
| <b>Diameter (mm)</b> :<br>12.70 ±0.05                                                                                                                   |
| <b>Thickness (mm)</b> :<br>0.50 ±0.05                                                                                                                   |
| <b>Coating</b> :<br>BBAR (2000-5000nm)                                                                                                                  |
| <b>Coating Specification</b> :<br>R <sub>avg</sub> <1.5% @ 2000-5000nm<br>R <sub>abs</sub> <3.0% @ 2000-5000nm<br>R <sub>avg</sub> <1.75% @ 2000-4000nm |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C)</b> :<br>8.8                                                                               |
| <b>Density (g/cm³)</b> :<br>3.97                                                                                                                        |
| <b>Edges</b> :<br>Fine Ground                                                                                                                           |
| <b>Index of Refraction n<sub>d</sub></b> :<br>1.77                                                                                                      |
| <b>Knoop Hardness (kg/mm²)</b> :<br>1900                                                                                                                |
| <b>Parallelism (arcmin)</b> :<br>≤3.5                                                                                                                   |
| <b>Poisson's Ratio</b> :<br>0.27                                                                                                                        |
| <b>Substrate</b> :<br>Sapphire (Al <sub>2</sub> O <sub>3</sub> )                                                                                        |
| <b>Surface Flatness (P-V)</b> :<br>2λ (typical)                                                                                                         |
| <b>Surface Quality</b> :<br>80-50                                                                                                                       |
| <b>Type</b> :<br>Protective Window                                                                                                                      |
| <b>Wavelength Range (nm)</b> :<br>2000 - 5000                                                                                                           |
| <b>Young's Modulus (GPa)</b> :<br>435                                                                                                                   |

## Regulatory Compliance

|                                                             |
|-------------------------------------------------------------|
| <b>RoHS 2015</b> :<br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance</b> :<br><a href="#">View</a> |
| <b>Reach 235</b> :<br><a href="#">Compliant</a>             |