

[See all 44 Products in Family](#)

**TECHSPEC® 12.7mm Dia x 100mm FL, VIS 0° Imaging Grade PCX Cylinder Lens**



Stock **#34-650** **4 In Stock**

1 MRP ₹11,227

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹11,227 each
Qty 6-25	₹10,075 each
Qty 26-49	₹9,547 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Type: Cylinder Lens, Plano-Convex

**Physical & Mechanical Properties**

Diameter (mm): 12.70 +0.0/-0.025

	<b>Bevel:</b>
Protective as needed	
<b>Center Thickness CT (mm):</b>	2.00
<b>Center Thickness Tolerance (mm):</b>	±0.1
<b>Clear Aperture CA (mm):</b>	11.43
<b>Edge Thickness ET (mm):</b>	1.61
<b>Optical Properties</b>	
<b>Effective Focal Length EFL (mm):</b>	100.00
<b>Substrate:</b> <input type="checkbox"/>	N-BK7
<b>f#:</b>	6.00
<b>Numerical Aperture NA:</b>	0.06
<b>Coating:</b>	VIS 0° (425-675nm)
<b>Wavelength Range (nm):</b>	425 - 675
<b>Back Focal Length BFL (mm):</b>	98.68
<b>Coating Specification:</b>	R <sub>avg</sub> ≤ 0.4% @ 425 - 675nm
<b>Radius R<sub>1</sub> (mm):</b>	51.68
<b>Surface Quality:</b>	40-20
<b>Power (P-V) @ 632.8nm:</b>	1.5λ
<b>Irregularity (P-V) @ 632.8nm:</b>	λ/4
<b>Plano Axis Wedge (arcmin):</b>	<5
<b>Power Axis Wedge (arcmin):</b>	<5

<b>Regulatory Compliance</b>	
<b>RoHS 2015:</b>	Compliant
<b>Certificate of Conformance:</b>	<a href="#">View</a>
<b>Reach 235:</b>	Compliant
<b>Country of Origin:</b>	China
<b>Imported By:</b>	Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Ideal for Beam Shaping Applications
- Tightly Controlled Optical and Geometric Tolerances
- Rectangular and Circular Form Factors Available

TECHSPEC® Imaging Grade PCX Cylinder Lenses offer an ideal pairing of tightly controlled tolerances and scalable pricing for volume integration. As opposed to spherical lenses, which focus light in two dimensions, cylinder lenses are used to focus light in one dimension. AR Coating options are available for laser applications, minimizing stray light and maximizing throughput of a system. Our TECHSPEC Imaging Grade PCX Cylinder Lenses are specified to control geometric characteristics in order to ensure consistent performance from design to manufacturing. Typical applications include circularizing elliptical beams from a laser diode, creating a light sheet for measurement systems, or projecting a laser line onto a surface.

**Note:** For negative focal length cylinder lenses, see our [TECHSPEC Imaging Grade PCV Cylinder Lenses](#).



## Coating Curves

---