

12.7mm Dia. 1064nm $\lambda/4$ Quartz Waveplate Multiple Order



Stock **#85-078** [CONTACT US](#)

-

1

+

₹22,359.00

ADD TO CART

Qty 1-5
₹22,359.00
Qty 6+
₹18,096.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
8.00

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Diameter (mm):
12.70 +0.00/-0.25

Substrate: Crystal Quartz
Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 6.40 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/10 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0015
Damage Threshold, By Design: 3.5 J/cm² @ 1064nm, 10ns
Retardance Order: Multiple Order

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View