

[See all 30 Products in Family](#)

## 12.7mm Dia., 355nm, $\lambda/2$ High Energy Waveplate



High Energy Quartz Waveplates

Stock **#25-447** **2 In Stock**

MRP ₹50,345

**Price inclusive of all taxes**

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹50,345 each
Qty 11+	₹41,466 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

High Energy Waveplate **Type:**

#### Physical & Mechanical Properties

8.0 **Clear Aperture CA (mm):**

12.70 **Diameter (mm):**

**Dimensional Tolerance (mm):**  
+0/-0.2

**Construction:**  
Optically Bonded on UVFS (C7980) Substrate

**Parallelism (arcsec):**  
<3

## Optical Properties

**Coating:**  
R<sub>avg</sub> <0.3%

**Design Wavelength DWL (nm):**  
355

**Substrate:**   
Crystalline Quartz

**Retardance:**  
λ/2

**Surface Quality:**  
20-10

**Transmitted Wavefront, P-V:**  
<λ/10 @ 632.8nm

**Retardance Tolerance:**  
λ/180 @ 20°C

**Damage Threshold, By Design:**   
>20 J/cm<sup>2</sup> @ 1064nm, 10ns, 10Hz

**Retardance Order:**  
1

## Threading & Mounting

**Mount Thickness (mm):**  
6 ±0.2

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Compliant](#)

**Country of Origin:**  
Lithuania

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Damage Threshold up to >20 J/cm<sup>2</sup> @ 1064nm
- λ/4 and λ/2 Retardance
- Black Anodized Aluminum Mount
- UV to NIR Design Wavelengths Available

High Energy Quartz Waveplates are available in both λ/4 and λ/2 retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to >20 J/cm<sup>2</sup> at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.